



# Ena Post

SECTION





MICROSCOPY



Perfect functional and esthetic integration with glass fiber post and composite  
Restoration made by Dr. Lorenzo Vanini


UV LIGHT



OPERATIVE & TECHNOLOGICAL ADVANTAGES

- Esthetic: fluorescent and dentin color
- Functional: same elasticity of dentin
- Perfectly integrated with the tooth, cement and restorative material
- The only post with silanized fibers inserted in the same resin of restorative material (Ena HRi)
- Perfect silanization
- Visible on X-ray only
- Colored rings for easy identification





Ref	Description	Q.ty
<b>CP0200</b>	<b>ESTHETIC POST KIT ENA POST 2% CONICITY:</b> Ena Post Fiber Post ø 0,8 - 1,25 mm Ena Post Fiber Post ø 1,0 - 1,45 mm Ena Post Fiber Post ø 1,2 - 1,65 mm Ena Post Fiber Post ø 1,4 - 1,88 mm Ena Post drill 1 x each size	5 pcs 5 pcs 5 pcs 5 pcs 4 pcs
<b>CP0208</b>	Ena Post Fiber Post white ring ø 0,8 - 1,25 mm	10 pcs
<b>CP0210</b>	Ena Post Fiber Post yellow ring ø 1,0 - 1,45 mm	10 pcs
<b>CP0212</b>	Ena Post Fiber Post blue ring ø 1,2 - 1,65 mm	10 pcs
<b>CP0214</b>	Ena Post Fiber Post black ring ø 1,4 - 1,88 mm	10 pcs
<b>CP0208-30</b>	Ena Post Fiber Post white ring ø 0,8 - 1,25 mm	30 pcs
<b>CP0210-30</b>	Ena Post Fiber Post yellow ring ø 1,0 - 1,45 mm	30 pcs
<b>CP0212-30</b>	Ena Post Fiber Post blue ring ø 1,2 - 1,65 mm	30 pcs
<b>CP0214-30</b>	Ena Post Fiber Post black ring ø 1,4 - 1,88 mm	30 pcs
<b>CPF0208</b>	Ena Post white ring drill ø 0,8 - 1,25 mm	1 pc
<b>CPF0210</b>	Ena Post yellow ring drill ø 1,0 - 1,45 mm	1 pc
<b>CPF0212</b>	Ena Post blue ring drill ø 1,2 - 1,65 mm	1 pc
<b>CPF0214</b>	Ena Post black ring drill ø 1,4 - 1,88 mm	1 pc

Ref	Description	Q.ty
<b>CP1000</b>	<b>ESTHETIC POST KIT ENA POST 10% CONICITY:</b> Ena Post Fiber Post ø 0,5 - 1,6 mm Ena Post Fiber Post ø 0,7 - 1,8 mm Ena Post Fiber Post ø 0,9 - 2,0 mm Ena Post Fiber Post ø 1,1 - 2,2 mm Ena Post drill 1 x each size	5 pcs 5 pcs 5 pcs 5 pcs 4 pcs
<b>CP1005</b>	Ena Post Fiber Post white ring ø 0,5 - 1,6 mm	10 pcs
<b>CP1007</b>	Ena Post Fiber Post green ring ø 0,7 - 1,8 mm	10 pcs
<b>CP1009</b>	Ena Post Fiber Post red ring ø 0,9 - 2,0 mm	10 pcs
<b>CP1011</b>	Ena Post Fiber Post blue ring ø 1,1 - 2,2 mm	10 pcs
<b>CP1005-30</b>	Ena Post Fiber Post white ring ø 0,5 - 1,6 mm	30 pcs
<b>CP1007-30</b>	Ena Post Fiber Post green ring ø 0,7 - 1,8 mm	30 pcs
<b>CP1009-30</b>	Ena Post Fiber Post red ring ø 0,9 - 2,0 mm	30 pcs
<b>CP1011-30</b>	Ena Post Fiber Post blue ring ø 1,1 - 2,2 mm	30 pcs
<b>CPF1005</b>	Ena Post drill (1 mark - white) ø 0,5 - 1,6 mm	1 pc
<b>CPF1007</b>	Ena Post drill (2 marks - green) ø 0,7 - 1,8 mm	1 pc
<b>CPF1009</b>	Ena Post drill (3 marks - red) ø 0,9 - 2,0 mm	1 pc
<b>CPF1011</b>	Ena Post drill (4 marks - blue) ø 1,1 - 2,2 mm	1 pc

